

TS SOLIDBAR DISPENSING UNITS
Especially Designed for Use with TS SOLIDBAR

AirKing 1 and 1A

Description

This electrical unit treats areas up to 940f² or 7520 f³, such as a two patient room in a hospital or a small dayroom. Made from high impact durable polymers, the unit features "4 way" ventilation for maximum airflow. The AirKing 1 and 1A hold 1-4 TS SOLIDBARS that fit in slots on the bottom of the dispenser. The AirKing 1A comes with a 3 prong plug.

Mounting

There are two methods to mount the machine. The machine can be permanently mounted using two screws (with anchors if needed) or wall mounted temporarily by placing a 1 inch screw in the wall. It's important to note that this unit needs to be placed near an electrical outlet. The machine can be opened by using the "L" shaped key provided with each order. The key is wedged into slots between the top and bottom of the machine and is used as a lever to pop open the back.

Cleaning

Use a clean soft cloth.

AirKing 2

Description

This battery operated unit is designed to treat up to 425 square feet or 3400 cubic feet. It uses 1 "D" cell battery and holds 1 SOLIDBAR or 4 MINIBARS. Unit has a white cover.

Mounting

This unit can be mounted on the wall or the back of a door using two sided tape or two 1 inch screws.

Cleaning

Use a clean soft cloth.

AirKing 3

Description

This passive unit is designed to treat areas up to 250 square feet or 2,000 cubic feet. The unit comes in white, gray or brown and has specially designed vents for efficient air circulation.

Mounting

This unit works best when placed on the back of a door. Each unit includes two 1 inch screws and 2 sided tape. Either can be used to mount the unit.

Cleaning

Use a clean soft cloth that can be immersed in a quaternary disinfectant.

AirKing 4

Description

The AirKing 4 holds 1-4 TS SOLIDBARS. This continuously running battery operated unit is designed to treat areas up to 875 square feet or 7,000 cubic feet. The unit requires 1 "D" cell battery. Features a vandal deterrent type cover and a L-shaped key.

Mounting

Each unit can be mounted with plastic anchors and screws.

Cleaning

Use a clean soft cloth.

AirKing 5

Description

The AirKing 4 holds 1-4 TS SOLIDBARS. This continuously running battery operated unit is designed to treat areas up to 875 square feet or 7,000 cubic feet. The unit requires 1 "D" cell battery. Features a vandal deterrent type cover and a L-shaped key.

Mounting

Each unit can be mounted with plastic anchors and screws.

Cleaning

Use a clean soft cloth

AirKing 12 and 36

Description

These units are designed to be attached to central air handling systems (HVAC). The distribution of the odor counteractant reaches every room and creates a fresh air effect. The AirKing 12 holds up to 12 TS SOLIDBARS. The AirKing 36 holds up to 36 TS SOLIDBARS.

Mounting

These units are mounted on the negative side of the plenum on the air handling unit or can be connected by a flexible hose.

Cleaning

Use a clean soft cloth that can be immersed in a quaternary disinfectant.

Mini Cabinet

Description

This unit will treat areas up to 125 square feet or 1,000 cubic feet. It is a passive unit specially designed for use with TS MINIBAR. Use in smaller areas with less extreme odor problems. The unit will also work using ½ of a regular size TS SOLIDBAR.

Mounting

Mount this unit in the appropriate areas using two sided tape.

Cleaning

Use a clean soft cloth that can be immersed in a quaternary disinfectant.

Easy-Mounts

Description

These cardboard mounts hold individual TS SOLIDBARS. This versatile unit can be mounted anywhere, even in obscure places such as around the baseboard or under furniture.

Mounting

Mount the unit using two sided tape included on back of unit.

Cleaning

These units should be discarded and replaced periodically.

